
Bar Hangers

IBERVILLE®



_	_
æ	7
O	Γ.
•	•

Cat. No.	Description / Usage
BAR HANGERS	
BK-01-CP	Adjustable hanger for wood stud. Length: 15.5 in. Height: 2.5 in.
1041-RT	Adjustable from 10-1/2 in. to 18 in. width
1042-RT	Adjustable from 14-1/2 in. to 25 in. width
1060CP	16 in. long support bracket. Grooved for use with device boxes with ears.
54151CFB-NW *	New work bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. (wood screws included) Maximum load capacity: Fan 70 lb. and fixtures 200 lb.
54151CFB-0W *	Rework bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. Maximum load capacity: Fan 70 lb. and fixtures 200 lb.

*cULus