

# Push-In Wire Connectors

**marrette**<sup>®</sup>



- **Temperature Rating:** 105 °C (221 °F) max.
- **Wire Range:** #24 to #12 solid or stranded tinned CU only
- **Flame Rating:** UL 94 V-2
- **Strip Length:** 11 mm (0.43 in.)

#### Features:

- Push-in design for fast connections
- Compact design
- Continuity test slot
- Colour-coded

#### Application Approval

cULus listed as a wire connector for 600 V max. building wire / 1,000 V max. in signs or fixtures.



Cat. No.	Number of ports	Colour	Wire Range	Packaging
PIC2B100	2	Light Grey	#24 to #12 solid or stranded tinned CU only	Window box of 100 units
PIC2M10				Clamshell of 10 units
PIC2BP250				Box of 250 units
PIC2BP1000				Box of 1,000 units
PIC3B100	3	Orange		Window box of 100 units
PIC3M10				Clamshell of 10 units
PIC3BP250				Box of 250 units
PIC3BP1000				Box of 1,000 units
PIC4B75	4	Red		Window box of 75 units
PIC4M10				Clamshell of 10 units
PIC4BP200				Box of 200 units
PIC4BP1000				Box of 1,000 units
PIC5M10	5	Yellow		Clamshell of 10 units
PIC5P				Propak of 100 units
PIC5BP200				Box of 200 units
PIC6M5	6	Grey		Clamshell of 5 units
PIC6P			Propak of 50 units	
PIC6BP100			Box of 100 units	
PIC8M5	8	Light Grey	Clamshell of 5 units	
PIC8P			Propak of 50 units	
PIC8BP100			Box of 100 units	