



2 Ports



3 Ports



4 Ports



5 Ports

- **Temperature Rating:** 105 °C (221 °F) max.
- **Wire Range:** #28 to #12 solid or stranded CU only
- **Flame Rating:** UL 94 V-2
- **Strip Length:** 12 mm (0.47 in.)

Features:

- Lever for easy insertion and release of wires
- Compact design
- Reusable
- Continuity test slot

Application Approval

cULus listed as a wire connector for 600 V max. building wire / 1,000 V max. in signs or fixtures.



Cat. No.	Number of ports	Colour	Wire Range	Packaging
LTC2M10	2	Blue	#28 to #12 solid or stranded CU only	Clamshell of 10 units
LTC2P				Propak of 100 units
LTC2BP500				Box of 500 units
LTC2BP1000				Box of 1,000 units
LTC3M10	3			Clamshell of 10 units
LTC3P				Propak of 100 units
LTC3BP500				Box of 500 units
LTC3BP1000				Box of 1,000 units
LTC4M5	4			Clamshell of 5 units
LTC4P				Propak of 50 units
LTC4BP250				Box of 250 units
LTC5M5	5			Clamshell of 5 units
LTC5P		Propak of 50 units		
LTC5BP250		Box of 250 units		