



External Cap

- Made of tough, durable polypropylene and 105°C rated to withstand high installation pressures.
- “Long-Wing™” design for smooth hand application. The long, off-set wings with raised edges offer a full-length, finger-friendly gripping surface. Torque can be selectively applied exactly where you want it:
 - Top - for tight finger locations
 - Bottom - for large wire bundles
- Ribbed body surface gives additional grip, even when hands are greasy or damp.
- Deep, wide throat ensures full insulation coverage.
- Threaded entry helps guide large wire bundles into the spring chamber.
- Colour-coded for quick and easy size selection.

Inner Spring

- “Live Action®” variable volume spring expands to accommodate a wide range of wire combinations.
- Square wire construction gives a positive conductor bite to solid or stranded wires.
- Unique copper-coated spring helps resist corrosion.
- Approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
- For copper conductors only.
- Convenient packaging - sized right and job-site ready!

For packaging options, see page D18



Model	Colour	20	18	16	14	12	10	8	6
739	Blue				Min.: 3 #12 + 1 #20	Max.: 2 #6			
Driver									
TOOL-WING	Plastic driver to install Model 739								

Nbr of Cond.	AWG	Nbr of Cond.	AWG	Nbr of Cond.	AWG	Nbr of Cond.	AWG	Nbr of Cond.	AWG	Nbr of Cond.	AWG
739				4	14	2	8	1	10	1	8
1	14	3	12	5	14	–	–	1	10	2	8
1	14	2	10	5	14	1	10	1	10	1	6
1	14	3	10	6	14	–	–	2	10	–	–
1	14	2	8	1	12	2	10	2	10	1	8
2	14	2	12	1	12	4	10	2	10	1	6
2	14	3	12	1	12	2	8	3	10	–	–
2	14	2	10	1	12	1	6	3	10	1	8
2	14	3	10	2	12	1	10	4	10	–	–
2	14	2	8	2	12	2	10	5	10	–	–
3	14	2	12	2	12	2	8	1	8	1	6
3	14	3	12	2	12	1	6	2	8	–	–
3	14	1	10	3	12	–	–	3	8	–	–
3	14	2	10	3	12	1	10	2	6	–	–
3	14	3	10	3	12	2	10				
3	14	2	8	4	12	–	–				
4	14	2	12	4	12	1	10				
4	14	1	10	5	12	–	–				
4	14	2	10	6	12	–	–				