



RT10-14VM6



RT10-6810VM6



RT14-14VM9



RT14-6810VM9



RT16-14VM9



RT16-6810VM9



ST10-10VM6



ST14-10VM9



ST16-10VM9



RT4-38NIM2

| Cat. No. | Colour / AWG | Material | Stud size | Packaging |
|-------------------------------|--------------------|----------|---------------|----------------------|
| RING TERMINALS | | | | |
| RT10-14VM6 | Yellow / 12-10 AWG | Vinyl | 1/4 in. | Clamshell of 6 units |
| RT10-38VM6 | | | 3/8 in. | |
| RT10-6810VM6 | | | #6 - #8 - #10 | |
| RT14-14VM9 | Blue / 16-14 AWG | | 1/4 in. | Clamshell of 9 units |
| RT14-246VM9 | | | #2 - #4 - #6 | |
| RT14-6810VM9 | | | #6 - #8 - #10 | |
| RT16-246VM9 | Red / 22-16 AWG | | #2 - #4 - #6 | Clamshell of 2 units |
| RT16-6810VM9 | | | #6 - #8 - #10 | |
| RT4-38NIM2 | 4 AWG | | Non insulated | 3/8 in. |
| RT6-14NIM2 | 6 AWG | | 1/4 in. | |
| SPADE (FORK) TERMINALS | | | | |
| ST10-10VM6 | Yellow / 12-10 AWG | Vinyl | #8 - #10 | Clamshell of 6 units |
| ST14-06VM9 | Blue / 16-14 AWG | | #4 - #6 | Clamshell of 9 units |
| ST14-10VM9 | | | #8 - #10 | |
| ST16-06VM9 | Red / 22-16 AWG | | #4 - #6 | |
| ST16-10VM9 | | | #8 - #10 | |



FB14-NFM9



FB16-NFM9



MB14-NFM9



MB16-NFM9



MFB14-NFM8



MFB16-NFM8

| Cat. No. | Colour / AWG | Material | Bullet size (in.) | Packaging |
|--|------------------|----------|-------------------|----------------------|
| FEMALE BULLET TERMINALS - FULL INSULATION | | | | |
| FB14-NFM9 | Blue / 16-14 AWG | Nylon | 0.156 | Clamshell of 9 units |
| FB16-NFM9 | Red / 22-16 AWG | | | |
| MALE BULLET TERMINALS | | | | |
| MB14-NFM9 | Blue / 16-14 AWG | Nylon | 0.156 | Clamshell of 9 units |
| MB16-NFM9 | Red / 22-16 AWG | | | |
| MALE / FEMALE BULLET TERMINALS | | | | |
| MFB14-NFM8 | Blue / 16-14 AWG | Nylon | 0.156 | Clamshell of 8 units |
| MFB16-NFM8 | Red / 22-16 AWG | | | |