

Armoured Cable / Flex Conduit Fittings

IBERVILLE®



2163



2166 / CI2172



Cat. No.	Alloy	Trade Size (in.)	Clamping Range (in.)		Suggested Applications		Packaging
			Min.	Max.	AC90 (BX)	Flexible Conduit	
ONE SCREW FITTINGS							
2163BP-35	Zinc	3/8	0.35	0.61	14/2; 12/2; 10/2; 14/3; 12/3; 10/3		Carton of 10 units
2163-V2-CP							Bag of 2 units
2163M2							Clamshell of 2 units
2166-V2-CP	Aluminum	1/2	0.50	0.90	8/2; 8/3; 8/4; 10/4; 1/1; 2/1		Bag of 2 units
2166M2							Clamshell of 2 units
2167M1							Clamshell of 1 unit
BC2167-V2		3/4	0.71	1.10	250/1 - 6/2		Each
BC2169-V2		1	1.16	1.50	250/1 - 300/1; 2/3; 4/4	1	
CI2170		1-1/4	1.32	1.77	400/1 - 600/1; 1/2; 1/3 - 2/0/3; 1/4	1-1/4	
CI2171		1-1/2	1.77	2.05	1000/1; 4/0/3; ACWU90: 1000/1; 4/0/3; 3/0/4	1-1/2	
CI2172		2	2.10	2.54	350/3 - 400/3; ACWU90: 1500/1; 500/2; 350/3 - 400/3; 250/4 - 300/4	2	