



XC-280 / CI2124



CI2173 / CI2174



CI4000



Cat. No.	Alloy	Trade Size (in.)	Clamping Range (in.)		Suggested Applications	
			Min.	Max.	AC90 (BX)	Flexible Conduit
TWO SCREW FITTINGS						
CI2104	Aluminum	1/2	0.45	0.59	14/2 - 10/2; 14/3 - 10/3; 14/4 - 12/4. ACWU90: 10/2; 12/3 - 10/3; 12/4; 12/5	5/16
CI2106		3/4	0.55	0.78	10/2 - 8/2; 10/3 - 8/3; 12/4 - 10/4 ACWU90: 3/1 -2/1; 8/2; 10/3 - 8/3; 10/4; 12/5	3/8 - 7/16
CI2108		1	0.69	1.01	1/0/1 - 2/0/1; 8/2 - 6/2; 8/3 - 6/3; 8/4. ACWU90: 3/1 - 3/0/1; 6/2 - 4/2; 8/3 - 4/3; 8/4 - 6/4	1/2
CI2110		1-1/4	0.84	1.33	1/0/1 - 350/1; 6/2 - 2/2; 6/3 - 2/3; 8/4 - 4/4; ACWU90: 1/0/1 - 400/1; 6/2 - 1/2; 6/3 - 2/3; 8/4 - 2/4	3/4
CI2112		1-1/2	1.06	1.57	4/0/1 -600/1; 2/2 - 1/2; 4/3 - 2/0/3; 4/4 - 1/4 ACWU90: 4/0/1-600/1; 1/0/2 - 3/0/2; 4/3 - 2/0/3; 6/4 - 1/0/4	1
CI2116		2	1.38	2.06	500/1 - 1000/1; 1/0/3 - 300/3; 1/4 - 3/0/4 ACWU90: 500/1 - 1000/1; 2/0/2 - 350/2; 1/0/3 - 300/3; 1/4 - 4/0/4	1-1/4 - 1-1/2
CI2120		2-1/2	1.95	2.47	400/3 - 500/3; 300/4 - 500/4	1-1/2 and 2
CI2124		3	2.25	3.57	500/4 - 750/4	2 and 2-1/2
CI2173		2-1/2	2.05	3.07	250/3 - 600/3; 250/4 - 300/4 ACWU90: 1500/1; 500/2	2 - 2-1/2
CI2174		3	2.25	3.57	350/3 - 600/3; 4/0/4 - 300/4 ACWU90: 1500/1; 500/2	2-1/2 - 3
CI4000		4	4.40	4.55		4
XC 280	Cast Aluminum Body and Clamp	3/8	0.18	0.64		

CI2120 is approved for all AC cables with diameter over armour between 1.95 in. and 2.47 in.
CI2124 is approved for all AC cables with diameter over armour between 2.25 in. and 3.57 in.