

Armoured Cable / Flex Conduit Fittings

IBERVILLE®



2175



CI2275



AMC0501-CP



Cat. No.	Alloy	Trade Size (in.)	Clamping Range (in.)		Suggested Applications		Packaging
			Min.	Max.	AC90 (BX)	Flexible Conduit	
DUPLEX FITTINGS							
2175M1	Zinc	3/8	0.15	0.65	14/2 - 10/2; 14/3 - 10/3; 14/4-12/4	3/8	Clamshell of 1 unit
2175-V2-MFP							Flip-Pak of 30 units
2175-V2-RP							Bag of 1 unit
CI2275*			0.45	0.58	14/2-10/2; 14/3-10/3; 14/4-12/4		Each

* Suitable for AC90 and ACG90. Clamping range for AC90: 0.45–0.58 and clamping range for ACG90: 0.47–0.57.



Cat. No.	Alloy	Thread (in.)	Range Over Jacket (in.)		Range Over Armour (in.)		Throat (in.)	Packaging
			Min.	Max.	Min.	Max.		
ALUMINUM FITTING								
AMC0501-CP	Aluminum	1/2	0.49	0.78	0.44	0.66	0.546	Bag of 2 units