



2210 / CI2236



CI2238 / CI2240



CI4090



CI5153



CI5154



| Cat. No.           | Alloy    | Trade Size (in.) | Clamping Range (in.) |                                            | Suggested Applications                         |                  | Packaging            |
|--------------------|----------|------------------|----------------------|--------------------------------------------|------------------------------------------------|------------------|----------------------|
|                    |          |                  | Min.                 | Max.                                       | AC90 (BX)                                      | Flexible Conduit |                      |
| 90 DEGREE FITTINGS |          |                  |                      |                                            |                                                |                  |                      |
| 2210M2             | Zinc     | 3/8              | 0.40                 | 0.63                                       | 14/2 - 10/2; 14/3 - 10/3; 14/4 - 12/4          | 3/8              | Clamshell of 2 units |
| 2210-V2-MFP        |          |                  |                      |                                            |                                                |                  | Flip-Pak of 30 units |
| 2210-V2-RP         |          |                  |                      |                                            |                                                |                  | Bag of 1 unit        |
| 2211M1             |          | 1/2              | 0.65                 | 0.97                                       | 8/2; 8/3; 10/4                                 | 1/2              | Clamshell of 1 unit  |
| 2211-V2-RP         |          |                  |                      |                                            |                                                |                  | Bag of 1 unit        |
| 2214M1             |          | 3/4              | 0.77                 | 1.12                                       | 1/0/1 - 4/0/1; 6/2 - 4/2; 8/3 - 3/3; 8/4 - 6/4 | 3/4              | Clamshell of 1 unit  |
| BC2214-V2          |          |                  |                      |                                            |                                                |                  |                      |
| CI2216             |          | 1                | 1.06                 | 1.40                                       | 4/0/1 -350/1; 2/2; 4/3 - 2/3; 6/4 - 4/4        | 1                |                      |
| CI2218             |          | 1-1/4            | 1.34                 | 1.65                                       | 500/1 - 750/1; 1/3 - 3/0/3; 1/4 - 1/0/4        | 1-14             |                      |
| CI2234             |          | 1-1/2            | 1.70                 | 2.15                                       | 600/1 - 1000/1; 2/0/3; 1/4 - 3/0/4             | 1-1/2            |                      |
| CI2236             | 2        | 1.51             | 2.47                 | 600/1 - 1000/1; 2/0/3 - 400/3; 1/4 - 4/0/4 | 1-1/2 - 2                                      |                  |                      |
| CI2238             | Aluminum | 2-1/2            | 2.50                 | 3.08                                       | 600/3 - 750/3                                  | 2-1/2            |                      |
| CI2240             |          | 3                | 2.95                 | 3.55                                       | 1000/3                                         | 3                |                      |
| CI4090             | Zinc     | 4                | 4.17                 | 4.62                                       |                                                |                  | 4                    |

| Cat. No.             | Alloy | Trade Size (in.) |      | Clamping Range (in.) |      |
|----------------------|-------|------------------|------|----------------------|------|
|                      |       | EMT              | FLEX | Min.                 | Max. |
| EMT / FLEX COUPLINGS |       |                  |      |                      |      |
| CI5153               | Zinc  | 1/2              | 3/8  | 0.17                 | 0.63 |
| CI5154               |       |                  | 1/2  | 0.75                 | 0.95 |