

Armoured Cable / Flex Conduit Accessories

IBERVILLE®



C10 / CI4



S-3 / S-4



38-V2-CP



CI7538



Cat. No.	Alloy	Hole Size (in.)	Clamping Range (in.)		Suggested Applications		Packaging
			Min.	Max.	AC90 (BX)	Flexible Conduit	
CABLE STRAPS							
C10	Aluminum	3/16	0.44	0.63	14/2		
1-V2-RP			0.50	0.56	12/2 - 10/2; 14/3 - 12/3; 14/4	5/16	Bag of 25 units
1M20							Clamshell of 20 units
1B100							Box of 100 units
CI2				0.63	10/3; 12/4	3/8	
3M10			0.57	0.68	10/2, 10/3, 12/4		Clamshell of 10 units
3-RP							Bag of 10 units
CI4			0.81	1.06	6/2; 6/3; 8/4	1/2	



Cat. No.	Alloy	Trade Size (in.)	Hole Size (in.)	Clamping Range (in.)		Suggested Applications		Packaging
				Min.	Max.	AC90 (BX)		
CABLE STAPLES								
S3B40	Steel			0.49	0.70	14/2-12/2; 14/3-12/3	5/16	Box of 40 units
S3M15								Clamshell of 15 units
S-3-V2-MFP								Flip-Pak of 250 units
S-3-RP								Bag of 10 units
S4B20				0.76	0.86	14/2-8/2; 14/3-8/3; 14/4-10/4	3/8, 7/16	Box of 20 units
S4M8								Clamshell of 8 units
S-4-V2-MFP								Flip-Pak of 100 units
S-4-RP								Bag of 10 units
FLEXIBLE CONDUIT STRAP								
38-V2-CP	Steel	3/8	3/16				Conduit up to 0.61 diameter	Bag of 25 units
ONE HOLE DOUBLE SIDED STRAP (GALVANIZED STEEL)								
CI7538*	Steel		3/16				1.05	

*Any combination of 3/8 in., 1/2 in. and 3/4 in., EMT, rigid conduit, flexible conduit or teck cables.