

Rigid Conduit Locknuts and Bushings

IBERVILLE®



BU 201 / BU 210



CI1704-AL / CI1732-AL



LN 201 / LN 210



2704 / CI2748



1704 / CI1748



CI2404 / CI2448



CI1704-SL / CI1732-SL



Trade Size (in.)	Locknuts					Bushings		
	Material					Zinc Die Cast	Insulated Aluminum	Plastic
	Steel	Aluminum	Nylon	Sealing	Zinc			
3/8			CI1703-PL					
1/2	1704 ¹	CI1704-AL	CI1704-PL	CI1704-SL	LN 201	BU201	CI2404 (ZINC)	2704 ⁶
3/4	1706 ²	CI1706-AL	CI1706-PL	CI1706-SL	LN 202	BU202	CI2406 (ZINC)	2706-V2-CP
1	1708 ³	CI1708-AL		CI1708-SL	LN 203	BU203	CI2408	2708-V2-CP
1-1/4	1710 ⁴	CI1710-AL		CI1710-SL	LN 204	BU204	CI2410	2710-V2-CP
1-1/2	1712-V2-CP	CI1712-AL		CI1712-SL	LN 205	BU205	CI2412	2712-V2-CP
2	1716 ⁵	CI1716-AL		CI1716-SL	LN 206	BU206	CI2416	2716-V2-CP
2-1/2	CI1720*	CI1720-AL			LN 207	BU207	CI2420	CI2720
3	CI1724*	CI1724-AL			LN 208	BU208	CI2424	CI2724
3-1/2	CI1728*				LN 209	BU209	CI2428	CI2728
4	CI1732*	CI1732-AL			LN 210	BU210	CI2432	CI2732
5	CI1740*						CI2440	CI2740
6	CI1748*							CI2748

* cULus Listed



Cat. No. 1	Packaging	Cat. No. 2	Packaging	Cat. No. 3	Packaging	Cat. No. 4	Packaging	Cat. No. 5	Packaging	Cat. No. 6	Packaging
1704-V2-CP	Bag of 10	1706-V2-CP	Bag of 10	1708-V2-CP	Bag of 5	1710-V2-CP	Bag of 4	1716BP-20	Box of 20	2704-V2-CP	Bag of 10
1704M5	Clampshell of 5	1706M5	Clampshell of 5	1708M5	Clampshell of 5	1710M4	Clampshell of 4	1716-V2-CP	Bag of 2	2704M4	Clampshell of 4
1704MP-50	Box of 50	1706MP-30	Box of 30	1708MP-15	Box of 15	1710MP-12	Box of 12	1716M3	Clampshell of 3		



CI2604 / CI2632



Trade Size (in.)	Insulated Grounding Bushings*	AWG Ground Wire Size
1/2	CI2604	14-6
3/4	CI2606	
1	CI2608	
1-1/4	2610-V2-CP	14-4
1-1/2	CI2612	
2	2616-V2	6-1/0
2-1/2	CI2620	
3	CI2624	2-4/0
3-1/2	CI2628	
4	CI2632	

* with solid copper lug