



1404 / 1416



CI1520 / CI1532



CI7538



Cat. No.	Alloy	Dimensions (in.)			Packaging
		Trade Size	Max EMT Diameter	Hole Diameter	
TWO HOLE EMT STRAPS					
1404-V2-CP	Galvanized Steel	1/2	0.71	3/16	Bag of 8 units
1406-V2-CP		3/4	0.92		Bag of 6 units
1408-V2-CP		1	1.16		Bag of 5 units
1410-V2-CP		1-1/4	1.51	1/4	
1412-V2-CP		1-1/2	1.74		
1416-V2-CP		2	2.20	3/8	
CI1520		2-1/2	2.88		
CI1524		3	3.50		
CI1528		3-1/2	4.00	1/2	
CI1532		4	4.50		
ONE HOLE DOUBLE SIDED STRAP					
CI7538*	Galvanized Steel		1.05	3/16	

*Any combination of 3/8 in., 1/2 in. and 3/4 in., EMT, rigid conduit, flexible conduit or teck cables.