



CI5153



5054-V2-CP / CI5058



BC5204-V2



BC5304-V2 / BC5306-V2 / CI5308-G / CI5310-G

-G: with gasket



Cat. No.		Trade Size (in.)			Clamping Range (in.)		Packaging
		EMT	Flex	Rigid	Min.	Max.	
EMT / FLEX COUPLINGS (ZINC ALLOY)							
CI5153	1/2	3/8		0.17	0.63		
CI5154		1/2		0.75	0.95		
SET-SCREW OFFSET BODY FITTINGS (ZINC ALLOY) CONCRETE-TIGHT							
5054-V2-CP	1/2			0.38		Bag of 1 unit	
CI5058	1			0.75			
PULL ELBOWS							
Cat. No.	Alloy	Trade Size (in.)	Dimensions (in.)		Suggested Applications		
			Height	Width			
BC5204-V2	Zinc	1/2	1-5/16	1-1/8	EMT to BOX		
BC5304-V2*		1/2	1-5/16	15/16	EMT to EMT		
BC5306-V2*		3/4	1-5/8	1-1/4			
CI5308-G		1	1-15/16	1-5/8	EMT to EMT with gasket		
CI5310-G		1-1/4	2-1/4	2			

*Not CSA Certified