



2-TB



3902BU



3902-TB



3112-U-CP



Cat. No.	Ground Wire Size	Water Pipe Size
2-TB	#6, #4, #2 AWG	1/2 in., 3/4 in., 1 in. or rebar 4-10
3-TB		1-1/4 in., 1-1/2 in. or 2 in.
4-TB		2-1/2 in., 3 in. or 3-1/2 in.
5-TB		4 in., 4-1/2 in. or 5 in.
6-TB		6 in.

Malleable iron crossbar, steel U-Bolt c/w copper cable clamp with serrations.

Cat. No.	Ground Wire Size	Water Pipe Size
3902-TB	#4-4/0 AWG	1/2 in.-1 in.
3903		1-1/4 in.-2 in.
3904		2-1/2 in.-3-1/2 in.
3905-TB		4 in.-5 in.
3906-TB		6 in.
3907		8 in.
3908		10 in.

Material: Steel U-bolt and nut c/w bronzed aluminum cap and crossbar cadmium plated plus gold chromate finish.

Cat. No.	Ground Wire Size	Water Pipe Size
3902BU*	#4-4/0 AWG	1/2 in.-1 in.
3903BU*		1-1/4 in.-2 in.
3904BU*		2-1/2 in.-3-1/2 in.
3905BU*		4 in.-5 in.
3906BU*		6 in.
3907BU*		8 in.
3908BU*		10 in.
3909BU*		12 in.

Material: Bronze U-bolt and nut c/w bronzed aluminum cap and crossbar with a brite dip finish.

*UL Listed for Direct Burial.

Cat. No.	Ground Wire Size		Water Pipe Size
	min.	max.	
3112-U-CP	10 sol.	2 str.	1/4 in.-2 in.

For connecting grounding conductor to water pipe. CSA approved for wet locations and for direct burial.