



**BE1-1 1/4INV-RT**



**BE1-1 1/4V**



**BE1-INTCV-RT**



**BE1-INV-RT**




**BE1-TCVGN-RT**



**BE1-VGN-RT**

## Product specifications

- Conductor range: 6–1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Before purchase or installation, verify acceptance with local utility.



Cat. No.	Description	Height (in.)	Width (in.)	Depth (in.)
<b>KING SIZE METER SOCKETS - 125 A - 600 V</b>				
BE1-1 1/4INV	Overhead, hub opening complete with 1-1/4 inches hub. Insulated neutral.	14-5/8	8-1/4	4-3/8
BE1-1 1/4V	Overhead, hub opening complete with 1-1/4 inches hub.			
BE1-INTCV-RT	Combination overhead-underground. Insulated neutral.			
BE1-INV-RT	Overhead, hub opening. Insulated neutral.			
BE1-TCV-RT	Combination overhead-underground.			
BE1-TCVGN-RT	Combination overhead-underground, comes with ground lug on neutral.			
BE1-V	Overhead, hub opening.			
BE1-VGN-RT	Overhead, hub opening, comes with ground lug on neutral.			