


BQ2-22VNH

BQ2-2VGN-RT

BQ2-2V

BQ2-TCV-CR

BQ2-TCVGN-RT

BQ2-TVGN-RT

BQ2-TV

BQ2-VGN-CR

BQ2-VGN-RT

BQ2-V-RT

Product specifications

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Before purchase or installation, verify acceptance with local utility.



Cat. No.	Description	Height (in.)	Width (in.)	Depth (in.)
STANDARD METER SOCKETS - 200 A - 600 V				
BQ2-22VNH	Overhead, twin hub opening.	15-5/8	8-47/64	5-13/32
BQ2-2VGN-RT	Overhead, twin hub opening comes with 2 in. hubs and ground lug on neutral.			
BQ2-2V	Overhead, hub opening comes with 2 in. hubs.			
BQ2-TCV-CR	Combination overhead-underground, corrosion resistant.			
BQ2-TCV	Combination overhead-underground.			
BQ2-TCVGN	Combination overhead-underground comes with ground lug on neutral.			
BQ2-TVGN-RT	Underground comes with ground lug on neutral.			
BQ2-TV	Underground.			
BQ2-VGN-CR	Overhead, comes with ground lug on neutral, corrosion resistant.			
BQ2-VGN-RT	Overhead, comes with ground lug on neutral.			
BQ2-V-RT	Overhead, hub opening.			