



**BS2-2INV**



**BS2-2V**



**BS2-INTCVBCCRRT**



**BS2-INTCV-RT**



**BS2-TCV-RT**



**BS2-V**

## Product specifications

- Conductor range: 6 AWG–250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Before purchase or installation, verify acceptance with local utility.



| Cat. No.                                      | Description   | Height (in.) | Width (in.) | Depth (in.) |
|---|---|--------------|-------------|-------------|
| <b>OVERSIZE METER SOCKETS - 200 A - 600 V</b> |   |              |             |             |
| BS2-2INV                                      | Overhead, hub opening comes with 2 in. hub. Ground lug on neutral.                | 17-1/8       | 12          | 5-7/16      |
| BS2-2V  | Overhead, hub opening comes with 2 in. hub.                                       |              |             |             |
| BS2-INTCVBCCR-RT                              | Combination overhead-underground comes with 3 in. knockouts. Corrosion resistant. |              |             |             |
| BS2-INTCVBC                                   | Combination overhead-underground comes with 3 in. knockouts.                      |              |             |             |
| BS2-INTCV-RT                                  | Combination overhead-underground comes with insulated neutral.                    |              |             |             |
| BS2-TCV-RT                                    | Combination overhead-underground.   |              |             |             |
| BS2-TCVBC                                     | Combination overhead-underground comes with 3 in. knockouts.                      |              |             |             |
| BS2-V   | Overhead, hub opening.  |              |             |             |