




**M02 SERIES**

## Product specifications

- Conductor range: line: single 1/2 in. studs to accommodate compression lugs 350 kcmil max. (supplied by utility), load: 6 AWG–250 kcmil
- For underground service only
- Aluminum tunnel type connectors for load side, 1/2 in. studs on line side
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- Before purchase or installation, verify acceptance with local utility.

 Copper or aluminum

Cat. No.	Description	Height (in.)	Width (in.)	Depth (in.)
<b>UNDERGROUND ONLY METER SOCKETS - 200 A - 600 V</b>				
M02-INV0	Underground 1/2 inch studs. Insulated neutral. (For Ontario)	19-1/8	12	5-9/16
M02-INV	Underground 1/2 inch studs. Insulated neutral.			
M02M-INV-RT	Underground 1/2 inch studs. Insulated neutral. 2/0 AWG subfeed on load side.			
M02M-V	Underground 1/2 inch studs. 2/0 AWG subfeed on load side.			
M02-V0	Underground 1/2 inch studs. (For Ontario)			
M02-V	Underground 1/2 inch studs.			