

Prefix Signification

<u>Prefix</u>	<u>Cu. in.</u>	<u>Description</u>
775	10.0	Gangable rework device box - 2-1/4 in. deep
777	11.0	Non-gangable rework device box - 2-1/4 in. deep
1004	15.0	Gangable device box - 3 in. deep
1100	8.0	Gangable device box - 1-1/2 in. deep
1102	10.0	Gangable device box - 2 in. deep
1104	12.5	Gangable device box - 2-1/2 in. deep
1110	16.5	Surface box - 1-7/8 in. deep
1304	14.5	Gangable device box - 2-1/2 in. deep
1504	15.0	Non-gangable device box - 2-1/2 in. deep
2004	18.5	Non-gangable device box - 2-3/4 in. deep
2020	14.0	Surface box - 1-7/8 in. deep
2104	12.5/gang	Non-gangable device box - 2-1/2 in. deep
2304	14.5	Non-gangable device box - 2-1/2 in. deep
3004	18.0	Gangable device box - 3 in. deep
3104	16.0	Gangable device box - 2-1/2 in. deep
4104	12.5	Communication box - 2-1/2 in. deep
52151	21.0	4 in. square box - 1-1/2 in. deep
52171	30.0	4 in. square box - 2-1/8 in. deep
53151	21.0	4 in. square extension - 1-1/2 in. deep
53171	30.0	4 in. square extension - 2-1/8 in. deep
54151	15.0	4 in. octagonal box - 1-1/2 in. deep
54171	21.0	4 in. octagonal box - 2-1/8 in. deep
55151	15.0	4 in. octagonal extension - 1-1/2 in. deep
56111	5.0	4 in. ceiling pan - 1/2 in. deep
72171	42.0	4-11/16 in. square box - 2-1/8 in. deep
73171	42.0	4-11/16 in. square extension - 2-1/8 in. deep
OBEX	5.0	4 in. round extension - 1/2 in. deep

Suffix Signification

<u>Suffix</u>	<u>Description</u>
K	Concentric knockouts (1/2 in. and 3/4 in.).
KSSX	Concentric knockouts (1/2 in. and 3/4 in.), mounting strap for steel stud installations and integral additional support bracket.
L	Clamps for nonmetallic sheathed cable and armoured cable.
LA	Clamps for armoured cable and nonmetallic sheathed cable.
LB	Clamps for nonmetallic sheathed cable and bracket (nailing style with prongs).
LD	Clamps for nonmetallic sheathed cable and “Swing-Arms” mounting device.
LH	Clamps for nonmetallic sheathed cable or armoured cable. Extended sides for external nailing.
LHA	Ideally for armoured cable but can also be used with nonmetallic sheathed cable. Extended sides for external nailing.
LHT	Clamps for nonmetallic sheathed cable or armoured cable. Extended sides for external nailing. Positioning tabs and 2 embossed mounting slots for internal screw installation.
LHTQ	LHT with “quick installation” feature. For new construction. Increase cubic capacity.
LLE	For nonmetallic sheathed cable or armoured cable without mounting ears.
LLE2	LLE but 2 gangs.
LLE3	LLE but 3 gangs.
LLE4	LLE but 4 gangs.
LF	Clamps for nonmetallic sheathed cable. Direct fan to box mounting.
LN	For nonmetallic sheathed cable or armoured cable staked nails.
LX	Self-locking spring clamps for nonmetallic sheathed cable.
LSSX	For nonmetallic sheathed cable or armoured cable, mounting strap for steel stud installations and integral additional support bracket.
LSSAX	For armoured cable or nonmetallic sheathed cable or, mounting strap for steel stud installations and integral additional support bracket.