




CI66-FPP



BC66-T



CI66-XL



CI66-XL-2



ASB SERIES



Cat. No.	Alloy	Width (in.)	Height (in.)	Suggested Applications AC90 (BX)	Packaging
PROTECTOR PLATES					
66-EP	Steel	1-3/8	3	For wood stud	Box of 50 units
66M4					Clamshell of 4 units
66P25					Box of 25 units
66-V2-RP					Bag of 5 units
66RPS-80					Rack Pack System of 80 units
CI66-FPP		2-3/8	3-1/2	For forenze	
66-SS-EP		4-3/8	1-7/8	For steel stud	Box of 25 units
BC66-T	Stainless Steel	4-1/4	3/4	For wood stud	
CI66-XL			3-3/4		
CI66-XL-2		8-1/2			

C.E.C. 2012 rule 12-516 (1) Where the cable is run through studs, joints, or similar members. The outer surface of the cable shall be kept distant at least 32 mm (1-1/4 in.) from the edges of the members or the cable shall be effectively protected from mechanical injury.

Cat. No.	Alloy	Nominal size (in.)	Suggested Applications AC90 (BX)	Packaging
ANTI-SHORT BUSHINGS				
ASB0-CP	Plastic	5/16	AC90: 14/2; 14/3; 1/2	Bag of 35 units
ASB1-V2-CP		3/8	AC90: 14/4; 12/3; 6/1; 4/1	Bag of 35 units
ASB234-CP		7/16 - 1/2 - 3/4	AC90 : #2: 12/4; 10/2; 10/3; 2/1 #3: 10/4; 8/2; 8/3; 1/1 #4: 8/4; 6/2; 6/3; 4/2; 4/3; 6/4	Bag of: 22 units x #2 4 units x #3 4 units x #4