

701

O.D. Pipe and Conduit Clamp for 4 in. conduit and higher
Machine screw and nut included.



Standard Finishes and Materials

PG = Pregalvanized (i.e. 701-045PG)

AL = Aluminum (i.e. 701-045AL)
with zinc plated hardware

SS6 = Stainless Steel Type 316
(i.e. 701-045SS6)

Cat. No.	O.D. of pipe		Conduit		Wt./C lb.	Std. Pack
	in.	mm	Rigid	EMT		
701-045PG	0.36-0.45	9-11.5	—	—	9	10
701-055PG	0.46-0.55	11.5-14	—	—	10	
701-065PG	0.56-0.65	14-17	—	—	11	
701-075PG	0.66-0.75	17-19.5	—	1/2	13	
701-088PG	0.76-0.88	19.5-22.5	1/2	—	15	
701-100PG	0.89-1.00	22.5-25.4	—	3/4	16	
701-113PG	1.01-1.13	25.5-29	3/4	—	17	
701-126PG	1.14-1.26	29-32	—	1	18	
701-140PG	1.27-1.40	32-36	1	—	18	
701-153PG	1.41-1.53	36-39	—	1-1/4	19	
701-167PG	1.54-1.67	39-42.5	1-1/4	—	20	
701-180PG	1.68-1.80	42.5-46	—	1-1/2	23	
701-193PG	1.81-1.93	46-49	1-1/2	—	26	
701-204PG	1.93-2.04	49-52	—	—	30	
701-225PG	2.10-2.25	53-57.5	—	2	32	
701-237PG	2.26-2.37	57.5-60	2	—	34	

Cat. No.	O.D. of pipe		Conduit		Wt./C lb.	Std. Pack
	in.	mm	Rigid	EMT		
701-245PG	2.33-2.45	59.95-62.5	—	—	36	5
701-257PG	2.46-2.57	62.5-65.5	—	—	38	
701-287PG	2.75-2.87	70-73	2-1/2	2-1/2	40	
701-294PG	2.88-2.94	73-75	—	—	42	
701-306PG	2.95-3.06	75-78	—	—	42.5	
701-319PG	3.07-3.19	78-81	—	—	43	
701-350PG	3.36-3.50	85.5-89	3	3	45	
701-356PG	3.51-3.56	89-90	—	—	46	
701-379PG	3.70-3.79	94-96.5	—	—	48	
701-400PG	3.80-4.00	96.5-101.5	3-1/2	3-1/2	49	
701-450PG	4.25-4.50	108-114	4	4	70	
701-556PG	5.25-5.56	121-141	5	5	75	
701-665PG	6.25-6.65	146-170	6	6	80	
701-876PG	8.50-8.75	197-222	8	8	85	